



# Tip Tinner

TT-95

Plato offers solder accessories like sponges, tip tinner, and bottles to improve your soldering process and increase your tip life.



## Renew oxidized tips with solder/cleaner combination

Plato's Tip-Tin provides fast, efficient cleaning and re-tinning of highly oxidized soldering iron tips safely and efficiently. This thermally-stable compound is lead-free, ESD, and environmentally safe. A well-tinned soldering tip improves operator performance and satisfaction. Just wipe the oxidized soldering tip at normal soldering temperature into the tip tinner for a few seconds until the bright tinning surrounds the working end of the tip. Wipe excess residue on a wet cellulose sponge.

- Extends life of tip
- Lead-free
- Halogen free
- Easy to use



## Product Packaging

TT-95  
Tip Tinner

10 units/case





---

## Instructions

Plato Tip Tinner is intended for periodic cleaning of soldering tips. A build-up of flux and oxides can cause a tip to stop wetting properly (called a "cold" tip). Roll the end of a hot soldering tip in Plato Tip Tinner. Then wipe the solder off on a damp sponge or brass tip cleaner. Finally re-tin the end of the tip with your wire solder.

NOTE: Plato Tip Tinner is not intended for tinning a tip at the end of the day or before a break. Tinning with wire solder is recommended to prevent the metal from oxidizing as the tip sits for a long period of time.

---

## Technical Information

### Chemical Composition

CHEMICAL NAME	CAS #
Copper	7440-50-8
Phosphoric acid, diammonium salt	7783-28-0
Tin	7440-31-5
Alcohols, C12-15, ethoxylated	68131-39-5

---

## Environmental Policy

Techspray is committed to developing products to ensure a safer and cleaner environment. We will continue to meet and sustain the regulations of all federal, state and local government agencies.

---

## Resources

Techspray products are supported by a global sales, technical and customer services resources.

For additional technical information on this product or other Techspray products in the United States, call the technical sales department at 800-858-4043, email [tsales@techspray.com](mailto:tsales@techspray.com) or visit our web site at: [www.techspray.com](http://www.techspray.com).

### North America

Techspray  
P.O. Box 949  
Amarillo, TX 79105  
800-858-4043  
Email: [tsales@techspray.com](mailto:tsales@techspray.com)

### Europe

ITW Contamination Control  
Saffierlaan 5  
2132 VZ Hoofddorp  
The Netherlands  
+31 88 1307 400  
Email: [info@itw-cc.com](mailto:info@itw-cc.com)

### Countries Outside US

Call to locate a distributor in your country.

Important Notice to Purchaser/User: The information in this publication is based on tests that we believe are reliable. The results may vary due to differences in tests type and conditions. We recommend that each user evaluate the product to determine its suitability for the intended application. Conditions of use are outside our control and vary widely. Techspray's only obligation and your only solution is replacement of product that is shown to be defective when you receive it. In no case will Techspray be liable for any special, incidental, or consequential damages based on breach of warranty, negligence or any other theory.

© 2015 Techspray, A Division of ITW

---



**Techspray**  
8125 Cobb Center Drive,  
Kennesaw, GA 30152  
800-858-4043 • [www.techspray.com](http://www.techspray.com)

